



REV.	DESCRIPTION	INITIATOR	DATE
01	INITIAL DRAWING	DJB	7/30/2018
02	ECO 17792; Updated Note 3.	MLS	3/20/2019



- NOTES:
1. OPTIONAL DOVETAIL ATTACHMENT FOR AXIAL MOUNTING.
  2. QUARTER TURN SINGLE AXIS LOCK OUT. TURN 90° TO ENGAGE OR DISENGAGE.
  3. APPROXIMATE WEIGHT 2.3 LBS, 1.04 KG.
  4. RADIAL COMPLIANCE TRAVEL AT COLLET = MAX  $\pm 5.5^\circ$  (APPROXIMATELY .22", 5.5mm).
  5. AXIAL COMPLIANCE TRAVEL AT COLLET = MAX .315", 8mm.
  6. COMPLIANCE AIR SUPPLY PRESSURE 15-60PSI, 1-4.1 BAR

NOTES: UNLESS OTHERWISE SPECIFIED.

DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN MILLIMETERS.




1031 Goodworth Drive, Apex, NC 27539, USA  
 Tel: +1.919.772.0115 Email: info@ati-ia.com  
 Fax: +1.919.772.8259 www.ati-ia.com  
 ISO 9001 Registered Company

PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.


DRAWN BY: D. Bohle 7/30/2018		TITLE	
CHECKED BY: B. Rose 7/30/2018		Compliant Deburring Blade Customer Drawing	
PROJECT #	170202-4	SHEET	1 OF 2
SCALE	2:3	SIZE	B
DRAWING NUMBER	9630-50-CDB-8-11	REVISION	02

# 9150-CDB-8-11-000



NOTES: UNLESS OTHERWISE SPECIFIED.

DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN MILLIMETERS.



1031 Goodworth Drive, Apex, NC 27539, USA  
 Tel: +1.919.772.0115 Email: info@ati-ia.com  
 Fax: +1.919.772.8259 www.ati-ia.com  
 ISO 9001 Registered Company

PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.

DRAWN BY: D. Bohle 7/30/2018		TITLE	
CHECKED BY: B. Rose 7/30/2018		Compliant Deburring Blade Customer Drawing	
PROJECT # 170202-4	SHEET 2 OF 2	SCALE 1:5	SIZE B
		DRAWING NUMBER 9630-50-CDB-8-11	REVISION 02